



DELEMIL-RS-S SERIES

Separation-type Nanofiltration Membrane

RS-S Series (Regular Separation) Nanofiltration Membrane Element utilizes special composite membrane that allows the monovalent salts to pass through while intercepting the divalent salts, as well as intercepting neutral molecule of about 150-300 Daltons molecular weight. It is mainly used in the desalination and concentration of dye, heavy metal removal, sodium chloride infiltration, sugar separation, concentration and desalination of whey protein, and concentration and desalination of titanium.

Membrane Parameter

Product Models	Average Flow Rate GPD (m³/d)	Average Rejection Rate %
RS-S 01	1950 (7.4)	98%
RS-S 02	1450 (5.5)	98%
RS-S 03	1900 (7.2)	98%
RS-S 04	1450 (5.5)	98%
RS-S 05	2450 (9.3)	96%
RS-S 06	1850 (7.0)	96%
RS-S 07	2350 (8.9)	96%
RS-S 10	8200 (31.0)	98%
RS-S 20	6600 (25.0)	98%
RS-S 30	8000 (30.3)	98%
RS-S 40	6250 (23.7)	98%
RS-S 50	10300 (39.0)	96%
RS-S 60	8200 (31.0)	96%
RS-S 70	10000 (37.9)	96%

Note: The average desalination rate is tested after 24 hours operation.

Flow fluctuation range of single membrane could be +25%.

Test Condition: 2000mg/LMgSO₄ solution, 580 psi operating pressure, 25°C temperature, pH=7, and 15% recovery rate.

Test membrane components of 2540 model are available.


Parameters of Membrane Operating and Cleaning

Parameters of Membrane Operating and Cleaning								
	Product Models	Max Operating Pressure	Pressure Drop of Single Membrane	Recovery Rate	Max Operating Temperature			
	RS-S Series	1200psi	<8psi	15%	60°C			
	Max Cleaning Temperature	PH Range of Continuous Working	PH Range of Cleaning	Allowable Max Contents of Residual Chlorine	Inlet Water			
	60°C	2-12	1-12	500ppm-h	NTU <1 SDI < 5			

Typical Application

- Acid electroplating wastewater recycling
- Dye removal or concentration
- Heavy metal removal
- Glauber's concentration
- BOD/COD removal, landfill leachate treatment
- Glucose purification, polysaccharide desalination, sugar concentration and grading
- Concentration of plant peptides and animal peptides

Membrane Schematics



Male Joint Membrane with ATD

Flat Joint Membrane with ATD



Specifications and Parameters

	Specifications	Joint	Diameter Inch (cm)			Package Weight
			Α	В	С	(kg)
	2540	Male Joint	40.00 (101.6)	0.75 (1.9)	2.4 (6.1)	3
	4040	Male Joint	40.00 (101.6)	0.75 (1.9)	3.9 (9.9)	4
	8040	Flat Joint	40.00 (101.6)	1.125 (2.85)	7.9 (20.1)	16

Special Notes:

- All membrane components are packed under the dry/semi-dry conditions;
- Each membrane element is equipped with an accessory kit, fitted with a connector and 4 O-rings.



Storage Conditions

Before the first use, all membrane elements must be stored under the original packaging conditions.

30°C may cause membrane degradation and deterioration of the protection solution.

- The membrane is best placed in the original packaging and opened before the using of water treatment system.
 The transport temperature below 0°C may cause irreversible membrane damage, and the transport temperature above
- Store in a cool, dry condition and the place where is not directly exposed to sunlight or artificial lighting. Storage temperature stays at 0°C to 30°C, and the longest storage time is 6 months.



General Information

- Once wetted, the membrane element must always be wet.
- The limited warranty we promised will expire due to the fact that the user does not strictly follow the operational restrictions and guidelines set forth in this Code.
- If the system is in a shut down state for a long time, the membrane element is advised to be placed in the protective solution to prevent the growth of microorganisms.
- It is the user's responsibility if use an incompatible chemical and lubricant, and cause undue influence on the original.
- The maximum allowable pressure drop of single pressure vessel is 60 psi (4.1bar).
- At no time can the backpressure be produced on the side of producing water to avoid the occurrence of harmful problems.